DIGITAL VERNIER CALIPER / DIGITAL VERNIER CALIPER WITH CARBIDE TIPPED MEASURING FACE 🔲 💬 🕕





For measurement of concave area▶

aliper Attachment



P163

Bluetooth BOX (separately sold) can be attached.

Measured value can be transmitted to PC wireless.

Standard model. Carbide tipped measuring face type is also available for measuring high-hardness, mold materials and rough-processing parts.



Reference standard for calibration

Block Gauge














SCRIBING CALIPER DEPTH

GAUGE HEIGHT **GAUGE**



Installation image of Bluetooth BOX (separately sold)

DIMENSIONS



Units: mm

Order No.	Α	В	С	D
GDCS-100	186	77	16.5	40
GDCS-150	236	//	10.5	
GDCS-200	286	90	19.5	50
GDCS-300	400	102	21.5	60
GDCS-150W	236	77	16.5	40
GDCS-200W	286	90	19.5	50
GDCS-300W	400	102	21.5	60
GDCS-150CD	236	77	16.5	40

Order No.	Α	В	С	D
GDCS-100	186	77	16.5	40
GDCS-150	236	//	10.5	
GDCS-200	286	90	19.5	50
GDCS-300	400	102	21.5	60
GDCS-150W	236	77	16.5	40
GDCS-200W	286	90	19.5	50
GDCS-300W	400	102	21.5	60
GDCS-150CD	236	77	16.5	40

(ϕ 1.9mm round depth bar)

% Quantization Error (± 1digit) not included

	% Qualitization End (⊥ Tulgit) not included							
Order No.	Model No	Туре	Measuring Range (mm)	Resolution (mm)	Accuracy ** (mm)	Depth Bar (Yes/None)	Weight	
151951	GDCS-100	Standard	0-100	0.01	± 0.03	Yes	155g	
151952	GDCS-150		0-150				175g	
151953	GDCS-200		0-200				200g	
151954	GDCS-300		0-300		± 0.04		260g	
151956	GDCS-150W	Carbide tipped	0-150		± 0.03		175g	
151957	GDCS-200W		0-200		1 0.03		200g	
151958	GDCS-300W		0-300		± 0.04		260g	
151955	GDCS-150CD	Round depth bar	0-150		± 0.03	Yes (φ1.9mm)	175g	

USE

•For outside diameter, inside diameter, step and depth measurement **MATERIAL**

Stainless steel

FEATURES

- Bluetooth BOX (separately sold) can be attached.
- Measured value can be transmitted to PC wireless.
- Available with carbide tipped measuring face. Suitable for measuring high-hardness, mold materials and rough-processing parts. (GDCS-150W·GDCS-200W·GDCS-300W)
- •GDCS-150CD (ϕ 1.9mm round depth bar)
- Display hold function
- •Auto power off function (after approx. 20 min.)

One CR2032 (lithium) battery included for testing

SK ПидаГа Seiki